

## Residential Electric Power Washer

# GENERAC®

## Power Washer



2700 psi - Model G0088880 (50-State & Canada)  
UPC: 696471083415

## FEATURES

### HIGH PERFORMANCE MOTOR

- Brushless motor for increased performance and durability

### MAINTENANCE FREE PUMP WITH EASY-ACCESS HOSE CONNECTIONS

- Prevents kneeling down on the ground

### 25FT HIGH PRESSURE HOSE

- Non-marring, kink resistant hose will not leave marks on the job

### AUTO-STOP SWITCH

- Automatically shuts off the pump when trigger is not engaged to save energy and prolong pump life

### ON-BOARD DETERGENT TANK

- Large 1 gal. detergent tank for easy soap application

### OVERSIZED NEVER-FLAT TIRES

- Improved mobility on rugged terrain

**2700 psi****specifications****PRESSURE AND FLOW**

|                                   |            |
|-----------------------------------|------------|
| Max Outlet Pressure (psi/bar)     | 2700/186.2 |
| Working Outlet Pressure (psi/bar) | 2100/144.8 |
| Max Flow Rate (gpm)/(L/min)       | 1.2/4.5    |

**ELECTRIC MOTOR**

|             |                    |
|-------------|--------------------|
| Motor Type  | Brushless (Copper) |
| Motor Watts | 1700               |
| Motor Volts | 120                |
| Motor Amps  | 13                 |

**POWER CORD**

|               |                     |
|---------------|---------------------|
| Type          | Cat. No. 16-14 AWG  |
| Length (ft/m) | 35/10.67            |
| GFCI Rating   | AC 125V, 60 Hz, 15A |

**PUMP**

|                                          |           |
|------------------------------------------|-----------|
| Type                                     | Axial Cam |
| Pump Material                            | Aluminum  |
| Maximum Water Supply Temperature (°F/°C) | 100/37.8  |

**HOSE**

|                    |                      |
|--------------------|----------------------|
| Hose Type          | PVC                  |
| Length (ft/m)      | 25/7.6               |
| Diameter (in/mm)   | 0.25/6.4             |
| Rating (psi/bar)   | 8700/600             |
| Connectors         | M22 Threaded         |
| Chemical Injection | Yes, 1 gal Chem Tank |

**NOZZLES**

|                     |                        |
|---------------------|------------------------|
| Nozzle Descriptions | (4) 0°, 15°, 25°, Soap |
|---------------------|------------------------|

**GUN & LANCE**

|                            |                      |
|----------------------------|----------------------|
| Gun Type                   | Ergonomic            |
| Gun to Lance Connection    | M22 Threaded         |
| Gun to Hose Connection     | Quick Change         |
| Lance Length (in/mm)       | 29.5/750             |
| Lance to Nozzle Connection | Quick Change         |
| Lance Material             | Steel, Chrome Plated |

**FRAME & MISC.**

|                    |                    |
|--------------------|--------------------|
| Handle             | Removable          |
| Frame Construction | Steel              |
| Wheels (in/cm)     | 12/30.5 Never Flat |

**DIMENSIONS & WEIGHTS**

|                               |           |
|-------------------------------|-----------|
| Length (in/mm)                | 21.4/545  |
| Width (wheel to wheel, in/mm) | 18.7/475  |
| Height (in/mm)                | 35.3/897  |
| Unit Weight (lbs/kg)          | 48.7/22.1 |
| Carton Length (in/cm)         | 19.5/49.5 |
| Carton Width (in/cm)          | 19.2/48.8 |
| Carton Height (in/cm)         | 21.7/55   |
| Carton Weight (lb/kg)         | 6.4/2.9   |
| Shipping Weight (lb/kg)       | 55.1/25.0 |

**WARRANTY**

|          |                |
|----------|----------------|
| Warranty | 2 Year Limited |
|----------|----------------|