



Exploded View : GP18000E 816 EFI PORT 50ST SEV
 Drawing No. : A0004012540

ITEM #	PART #	QTY	DESCRIPTION
1	A0005075631	1	ST47 WELD FRAME WITH SPANNER 816 CC PORT
2	082121C	1	CLIP-J VINYL COAT .625 ID
3	A0001664520	12	SCREW BHSC M8-1.25 X 45MM BLACK
4	A0001443510	1	ST19 WELDMENT SIDE PANEL EXH
5	I0000031500	2	HANDLE GRIP GP
6	A0001403831	2	ST47 HANDLE TUBE STRAIGHT
7	0H1779	6	SCREW HHFC M8-1.25 X 45 G8.8
8	A0000430785	2	DECAL PINCH POINT HAZARD
9	G049820	2	NUT HEX LOCK M8-1.25 NY INS
10	G066849	2	SCREW HHTT M5-0.8 X 16
11	065442	2	SNAP BUTTON - .437" DIA. HEAD
12	A0003127664	1	ST47 HEAT SHIELD CONTROL PANEL AVR
13	0K9160	9	SCREW HHFCS M6-1.0 X 10 G8.8 ZB
14	A0003236229	1	ST47 HEAT SHIELD FUEL TANK AEGIS
15	A0000745470	1	ASSY FUEL TANK 14.3GAL GENERAC ORANGE
16	065445	5	SCREW HHTT M8-1.25 X 20
17	A0000335997	1	ASSY PUMP FUEL PORT GASOLINE
18	A0000912834	1	ST11 BRACKET FUEL PUMP COVER CLEAR ZINC
19	A0000660794	1	COVER FUEL PUMP BLACK
20	0E1644	2	SCREW BHSC M6-1.0 X 12 SS
21	G049815	6	SCREW HHC M5-0.8 X 16 G8.8
22	G051713	6	WASHER FLAT M5
23	063662A	1	CLAMP HOSE STEPLESS 14.5
24	A0000886608	1	ASSY HOSE FUEL WITH QUICK CONNECT
25	048031C	4	CLAMP HOSE BAND .50
26	0L1113	1	CANISTER CARBON 1200CC
27	0D5202	1	NUT WING 5/16-18 BRASS
28	G029809	1	NUT HEX 5/16-18 BRASS
29	0D5199	4	WASHER FLAT 5/16 BRASS
30	0C3168	4	WASHER LOCK SPECIAL 5/16
31	0D5198	1	SCREW HHC 5/16-18 X 1-1/2 BR
32	060999B	1	FAN ASM 10X1.50 BORED
33	I0000021307	1	STR-102-17.5 ADI PORT (2017)
34	I0000021319	1	RTR-102-17.5 ADI PORT (2017)
35	A0002426718	1	ASSEMBLY BRUSH HOLDER
36	0G2551	1	WASHER FLAT HRD ST 0.438 X 1 ZCY
37	G022237	1	WASHER LOCK SPRING 3/8 ZC
38	0D1838	1	SCREW HHC 3/8-24 X 15.50
39	0J0772	1	CLIP SNAP-IN WIRE MANAGEMENT
40	A0000693305	1	REAR BEARING CARRIER MACHINED
41	0C7758	6	VIB MNT 1.5 X 1.38 X 5/16-18
42	G022129	10	WASHER LOCK SPRING 5/16 ZC
43	0D3549	4	SCREW IHHC M8-1.25 X 400 G8.8
44	A0000693312	1	REAR BEARING CARRIER COVER
45	A0001472508	4	SCREW HHTT #10-32 X 1-1/4 CZ
46	A0001017560	1	ASSY MUFFLER SIDE MOUNT 816CC PORT
47	A0002455480	3	HANGER EXHAUST FLEXIBLE EPDM
48	A0001464800	1	ST47 BRACKET EXHAUST HANGER RIGHT
49	151921	2	PIN HITCH CLIP 5/16-3/8
50	A0001478920	2	CLEVIS PIN 3/8" X 1 1/4" USABLE BLACK
51	G045764	1	SCREW HHTT M4-0.7 X 8 ZP
52	0D5133	1	SCREEN SPARK ARRESTOR
53	0D5133A	1	RETAINER, SPARK ARREST SCREEN
54	0G0926	1	SCREW HHFCS M6-1 X 16 G8.8
55	A0001525113	1	HEAT SHIELD MANIFOLD 816CC
56	I0000047151	1	SENSOR OXYGEN SWITCHING 12MM HEX
57	A0002846615	2	BOLT U 5/16-18 X 1.92 W/SADDLE
58	A0002197660	1	PIPE FLEX EXHAUST, FL 48MM ID
59	A0001196675	1	ASSY WELDMENT EXHAUST MANIFOLD EPT
60	G040976	4	SCREW SHC M8-1.25 X 20 C12.9
61	0C4138	2	GASKET EXHAUST PORT
62	0H3535	6	NUT HEX FLANGE M5-0.8 LOCK NYLON
63	A0001443509	1	ST19 WELDMENT SIDE PANEL CNTRL
64	A0000509466	1	MODULE CO PORTGEN V2.5 EFT
65	A0000944983	1	SHROUD SIDE PANEL CONTROL BLACK GP18KW
66	G057593	2	CABLE TIE MOUNT BLACK
67	A0000766703	1	DECAL BRANDING CP SIDE GP
68	A0001642218	1	BADGE CO-SENSE V2.5 GP15.5/GP18
69	Order #175	1	CONN HSG 4POS DL SEALED SERIES
70	Order #175	1	WIRE BUNDLE FUEL PUMP LEADS
71	0E6480	16	NUT HEX LOCK M4-0.7 NY INS
72	A0002528123	1	ST47 COVER CONTROL PANEL ALT WIRES
73	G082025	5	NUT HEX LOCK M5-0.8 NYINS ZINC
74	0F97190SRV	1	ASSY PCB VREG AIR COOLED 2006
75	G075235	2	SCREW HHC M5-0.8 X 30 C8.8
76	A0003128317	1	ST47 AVR MOUNT BRACKET
77	0J9125	14	NUT HEX FL WHIZ M8-1.25

ITEM #	PART #	QTY	DESCRIPTION
78	0H1780B	2	CURVED HEAD M8-1.25 X 50MM LNG
79	0H6559	10	NUT HEX FLANGE WHIZ 5/16-18
80	G097400	1	CSA HIPOT DECAL
81	0K9502A	1	DECAL SPARK ARRESTOR MATTE
82	I0000003425	1	DECAL FUEL OVERFLOW PRO SERIES
83	0H0116B	1	DECAL WARN HOT EXHAUST
84	0H8250B	1	DECAL CO WARNING 3L PRODCOT HOR
85	I0000033027	1	DECAL CO-SENSE ACTION LABEL
86	0H4635C	1	DECAL DANGER & SAFETY PGMA
87	A0001642211	1	DECAL CLEAR POWERRUSH GP
88	A0000766705	1	DECAL START INSTRUCTIONS GP 816CC PORT
89	0H0176	1	TAG, OIL FILL TRILINGUAL
90	0G9391	2	COVER, 30A 120/240V
91	067210D	1	DECAL GROUND
92	Order #175	1	BACK BOX CONTROL PANEL 816 BLACK
93	Order #175	1	SNAP BUSHING .70 OPEN
94	Order #175	1	SNAP BUSHING .50 OPEN
95	G032300	2	HOLDER FUSE
96	0D4804B	1	XFMR IDLE CURRENT
97	0F539650AR	1	MX150L SLRRMNT 22-18 12P W/OGA
98	G048505	1	CB 6A 1P AUTO ETA 46-500-P
99	Order #175	2	SCREW PPHM SEMS M4-0.7 X 12
100	G052813	2	SCREW HHC M4-0.7 X 20 C8.8
101	G045770	3	SCREW HHC M5-0.8 X 10 C8.8
102	G052844	3	RELAY PNL 12VDC SPDT 30A
103	Order #175	2	DIO BRIDGE RECT 25A 1000V KBPC
104	Order #175	1	CONN, PLUG HOUSING DUAL ROW 14 POS, UL 94V-0
105	Order #175	1	CONDUIT FLEX 14.5MM ID NYLON 6
106	Order #175	4	SNAP BUSHING.75 OPEN
107	G049813	3	NUT HEX M6-1.0 G8 CLEAR ZINC
108	G022097	4	WASHER LOCK SPRING 1/4 ZC
109	G022473	6	WASHER FLAT 1/4-M6 STEEL ZINC
110	G057405	1	MOUNTING CLIP RES 25R 5X 25W
111	0A2053	1	SCREW HHC M6-1.0 X 65 C8.8
112	Order #175	1	FACEPLATE CONTROL PANEL 816 PORT
113	G051715	2	NUT HEX M4-0.7 G8 YEL CHR
114	Order #175	2	SELF TAPPING SCREW ST4.8X13
115	Order #175	3	PANEL FEED-THROUGH, SCREW CONNECTION
116	0K3130	8	SCREW PPPH M5-0.8 X 16 BZC
117	Order #175	1	DECAL CONTROL PANEL GP18KW
118	Order #175	1	CB 0050A 2P 240V
119	Order #175	1	CB 0030A 2P 240V
120	0D4969	1	OUTLET 50A 125/250V 4W 1258
121	G075207	2	CB 0020A 1P UL/CSA SANG MAO
122	0G8321	1	OUR METER W/ALERTS AC/DC
123	Order #175	1	LIGHT MALFUNCTION INDICATOR RED
124	0H0265E	1	CB 30A 1P CUL/CSA
125	A0001177764	1	SWITCH KEY
126	A0000961590	1	SWITCH KEY ACTUATED START
127	0A1658	2	WASHER LOCK SPECIAL 1/4"
128	G045757	1	SCREW HHC M6-1.0 X 25 C8.8
129	Order #175	1	WIRE ASSY GROUND 8AWG GREEN/YELLOW
130	G068868	1	OUTLET 30A 120V RECEP
131	0E8388	1	NUT HEX FL WHIZ M6-1.0
132	0G8758	1	OUTLET 30A 120/250V SPCGR
133	0D4966	2	OUTLET 20A 120V GFCI GF20BK
134	0G9392	2	COVER, 20A 120V GFCI/DUPLEX
135	0H3814	1	COVER 50A 120/240V
136	Order #175	8	SCREW PPHM SEMS M3-0.5 X 6
137	A0002363505	2	WHEEL 12"OD NEVERFLAT RUBBER
138	G045900	4	WASHER FLAT 3/4 STEEL ZINC
139	A0000660498	1	AXLE 19 DIA X 773.7 CLR ZINC
140	G027007	2	VIB MOUNT-DONUT TYPE
141	G050190	2	WASHER FLAT .344ID X 1.00D STEEL
142	G042909	2	SCREW HHC M8-1.25 X 30 C8.8
143	A0000961686	2	ST47 WELDMENT FOOT 816 PORT
144	I0000036414	2	SCREW HHFC M8-1.25 X 16 C8.8
145	A0001002982	2	ST47 GUSSET FOOT 816 PORT
146	0D3545	2	J-BOLT M8-1.25 X 225
147	0D4565	1	BRACKET BATTERY
148	G022145	6	WASHER FLAT 5/16-M8 STEEL ZINC
149	G045771	2	NUT HEX M8-1.25 G8 CLEAR ZINC
150	G022127	2	NUT HEX 1/4-20 STEEL
151	G075763	1	BOOT BATTERY CABLE
152	G022287	2	SCREW HHC 1/4-20 X 3/4 G5
153	N/A	1	BATTERY BCI GROUP UI
154	G022259	2	NUT HEX 5/16-18 STEEL

ITEM #	PART #	QTY	DESCRIPTION
155	A0000944991	1	ST47 BRACKET ENGINE MOUNT GP
156	G067989	4	NUT HEX FL WHIZ M8-1.25
157	G051731	4	SCREW HHC M8-1.25 X 50 C8.8
158	I0000045702	1	ENGINE GH816 EPT 50 ST W/COOLER
159	A0004429626	1	PRGMD ENGINE CONTROL MODULE-46 PIN EFT
160	0B2236	4	NUT HEX LOCK M6-1 NY INS
161	A0003294167	1	CABLE BATT RED #6 X 19 PRTBL
162	0388050AF0	1	CABLE BATT BLK #6 X 13 PORTBLE
163	075763A	1	BOOT, BATTERY CABLE
164	0C2417A	1	EARTH STRAP 3/8X 3/8
165	0H3443	2	COTTER HAIRPIN 2.56 X .80
166.1	077043D	7 IN	CONDUIT FLEX .625ID
166.2	077043D	17 IN	CONDUIT FLEX .625ID
167	I0000031512	2	SCREW BHFH TORX M5.5-1.59 X 15
168	0H0958A	1	ASSY GAS CAP SEALED - BLACK
169	A0003330316	1	KIT-HANDLE ASSEMBLY
170	A0003330700	1	KIT-FUEL TANK ASSEMBLY
171	A0003330680	1	KIT-MUFFLER ASSY
172	A0003347459	1	KIT-ALTERNATOR ASSEMBLY
173	A0003347318	1	ASSEMBLY-ROTOR/STATOR
174	A0003330604	1	KIT - COMMON DECALS
175	A0000697966	1	CONTROL PNL ASSY GP18KW
176	A0003330493	1	KIT-CO-MODULE - GP18KW
177	A0003330326	1	KIT-WHEEL ASSEMBLY
178	A0003330321	1	KIT-FOOT BRACKETS
179	A0003330686	1	KIT - BATTERY ASSEMBLY
180	A0003330009	1	KIT-GROUNDING WIRE TO FRAME
181	A0001077246	1	FUEL GAGE ROUND 187LG ARM
182	A0000937729	1	HOSE FUEL 1/4" ID X 16.32" LG
183	A0000961602	1	HOSE EVAP 1/4" ID X 47.8" LG
184	A0001657007	1	ST47 BRACKET CARBON CAN GP
185	A0001664513	2	SCREW SHC M8-1.25 X 170 C12.9
186	A0004007317	1	KIT CARBON CANNISTER ASSEMBLY