

iQ5200DF

Specifications

Product Series	iQ5200DF
Model Number (Configuration)	G0089450 (iQ5200 49ST) G0089470 (iQ5200 50ST)
AC Rated Output Running Watts	3900 (Gasoline) / 3500 (LP)
AC Maximum Output Starting Watts	5200 (Gasoline) / 4700 (LP)
Rated AC Voltage	120 VAC
Rated AC Frequency	60 Hz
Rated 120 VAC Amperage	32.5 (Gas) / 29.2 (LP)
Engine Displacement	223cc
Engine Type	OHV
Engine RPM	Variable
Recommended Oil	10W-30 / SAE 30
Oil Capacity qt (L)	0.6 (0.6)
Lubrication Method	Splash
Total Harmonic Distortion	< 3% (safe for sensitive electronics)
Choke Location	Auto-Choke
Fuel Selection	On Control Panel
Starting Method	Electric Start / Recoil Pull Start
Battery Included	Yes

Battery Type	Lead Acid (12V DC, 6 Ah)
Battery Part No.	10000038386
Battery Dimensions	4.5" X 2.8" X 5.2"
Low Oil Shutdown	Yes
Neutral Bonded to Ground	Yes
Start Switch Type	Push Button
Start Switch Location	On Control Panel
Fuel Tank Capacity US gal (L)	3.2 (12)
Run Time at 50% of Rated Load (Hours)‡	9 (Gasoline) / 11 (20lb LP Tank)
Run Time at 25% of Rated Load (Hours)‡	15 (Gasoline) / 20 (20lb LP Tank)
Warranty - Residential	3 Year Limited
Warranty - Commercial	2 Year Limited
Included	Engine oil, oil funnel, battery, tool kit and Owner's Manual, propane hose
Economy Mode	Yes

Dimensions and Weights

iQ5200DF	
Extended Length in (mm)	37.2 (944)
Length in (mm)	24.6 (625)
Width in (mm)	20.3 (515)
Extended Height in (mm)	23.4 (594)
Height in (mm)	22.5 (572)
Carton Length in (mm)	25.8 (655)
Carton Width in (mm)	22.4 (570)
Carton Height in (mm)	24.2 (615)
Unit Weight lbs (kg)	111 (50.3) 49/50ST
Shipping Weight lbs (kg)	126 (57.1) 49/50ST

