

OL3213\$

REFERENCE DRAWINGS

OL3237 INTECONNECTION DIAGRAM 6-800A
OL3245 SD / VD 600-800A 1PH
OL3238 INSTALLATION DRAWING
OL3204 MANUAL
* OL3250 HARNESS- 1Ø

* NOT SHOWN

SEE PAGE 2 (DETAIL 'C')
FOR WIRE DUCT CUT LIST

SEE PAGE 2 (DETAIL 'B')
FOR SUBPLATE ASSY.

SEE PAGE 2 (DETAIL 'A')
FOR DOOR DECAL LOCATION

ATS-X

JUMPERS


REF. ONLY
TERMINAL BLOCK
ON TRANSFER SW.
JUMPERS FROM HARNESS

MOUNTING (600A)
TORQUE TO 360 IN.-LBS.
MANUFACTURING NOTES:


ITEM #	PART #	REV #	DESCRIPTION
100	038150	2	WASHER FLAT Ø8 ZINC
101	028864	2	WASHER LOCK Ø8-M4
102	038715	2	NUT HEX M4-0.7 Ø8 YEL CHR
103	027580	1	NUT WING M6-1.0
104	013648	2	SCREW THIT M6-0.5 X 25 ZP
105	028155	8	WASHER LOCK M10
106	024455	6	WASHER SHAKESHEED EXT 5/16 STL
107	028190	9	WASHER LOCK 1/2
108	028196	9	NUT HEX 1/2-13 STEEL
109	023016	9	SCREW HMC 1/2-13 X 4 SS
110	028992	7	SCREW THIT Ø8-32 X 1/4 CZ
111	067989	4	NUT HEX FL M12 M8-1.25
112	048911	6	SCREW HMC M10-1.5 X 30 GB. 8
113	045385	6	WASHER LOCK M10
114	091477	2	RIVET, WIRE DUCT MNT
115	043764	6	SCREW THIT M4-0.7 X 8 ZP
116	041495	2	SCREW THIT M4-0.7 X 10 ZP

ITEM #	PART #	REV #	DESCRIPTION	QTY
1	01091	1	CHCL NEMA 3R 30X60X200 RTS	-
2	REF. MODEL	1	DECAL RTS TRANSFER SWITCH 3R	-
3	095882	1	DECAL-LIVE CIRCUIT	-
4	028994	1	DECAL-ENCLOSURE NOTE NEMA 3R	-
5	031494	1	DECAL-UL CONTROL PANEL ENCL.	-
6	01095	1	DECAL RTS TEST SEQUENCE 600A	-
7	03886190	1	ASSY WIRE Ø12.00" (GROUND WIRE)	-
8	078154	REF.	MAN. WBL Ø-1600A UNSUPPLIED W/900	-
9	074525	1	DECAL, MANUAL OPERATION	-
10	078111	1	XFERSW 600A 3P UNMOV	-
11	089433	9	LUG SLUGS 500-M1X3/32 AL/CU	-
12	074349A	2	CVR CYR M1 600A 3P	-
13	074351	2	CVR BRKT 600-1600A RH	-
14	074351A	2	CVR BRKT 600-1600A LH	-
15	063986	4	CHUB COVER M12-3-30HA	-
16	063986	2	DECAL TERMINAL SHOCK HAZARD	-
17	064310	1	DECAL-TERMINAL NOTE	-
18	038700	1	ASSY NEUTRAL BLK 600-1000A ATS	-
19	044557	1	DECAL NEUTRAL	-
20	065884	1	ASSY GRD TERM 1600-2600A	-
21	047810A	1	DECAL, GND	-
22	0109003114	1	SUB-PLATE RTS 600-800A	-
23	REF. MODEL	1	PLATE DATA - RTS	-
24	063617	1	RELAY PNL 12VDC DPDT 10A8E40VA	-
25	038886	1	FUSELOCK 30A 600V EPDS V/SD	-
26	038772	1	FUSELOCK 30A 600V SPDS V/SD	-
27	073590A	3	FUSE SA X BUSS	-
28	0379937	1	TERM BLK 3P UL 18-20AWG	-
29	04917	1	DECAL CUSTOMER CONN. RTS	-
30	054199	1	DECAL DANGER HIGH VOLTAGE	-
31	091478	FT	DUCT WIRING 1X1.5 (3P+G 780FT)	-
32	091478A	FT	COMMON WIRE DUCT 1 IN (3P+G 780FT)	-
33	074465	4	TIE-BAND MOUNT FIT THREE CIRCLED	-
34	013650	1	WIRE HARNESS 600-800A MDE V/SACH	-
35	0244195	1	DECAL FUSE RATING SA 600V	-
36	049774	1	DECAL NEC COMPLIANCE	-
37	049770	1	CHANNEL SWAPTRACK 76.2 X 191.2	-
38	013123	1	ASSEMBLY SHUNT AC MODULE	-


* DESIGNATES ITEMS STRUCTURED IN WIRE HARNESS CHIT SHOWN



LEFT SIDE VIEW



FRONT VIEW



RIGHT SIDE VIEW

GENERAC PART NUMBER	DESCRIPTION	ITEM #	ITEM #
OL3213	ASSEMBLY 600A NSE	0K1098	0K1799N
OL3213A	EXPLODED VIEW DRAWING	N/A	N/A
OL3213B	ASSEMBLY 600A NSE	0K1274	0K1799N

SHEET 1 OF 2

DATE "A" RELEASED FOR PRODUCTION

THIS DRAWING IS THE PROPERTY OF GENERAL ELECTRIC COMPANY. IT IS TO BE KEPT IN THE OFFICE OF THE ENGINEER OR DESIGNED BY AND NOT TO BE REPRODUCED OR COPIED IN ANY MANNER WITHOUT THE WRITTEN PERMISSION OF THE COMPANY.

DO NOT SCALE

DATE 03/30/18

DATE 03/30/18

DATE 03/30/18

DATE 03/30/18

DATE 03/30/18

DATE 03/30/18

DATE 03/30/18

AV 600A RTS
NEMA 3R W/SMART AC MOD.

SEE NOTES

GENERAL ELECTRIC COMPANY
BY: [Signature]
WATSONVILLE, CA 95076

DATE 03/30/18

DATE 03/30/18

DATE 03/30/18


DATE 03/30/18

1 - 5 2015 SACM

OL3213\$


A

OL3213\$	
----------	--



DETAIL "A"


DOOR-FRONT
DECAL LOCATION
SCALE 1.5X



DETAIL "B" DETAIL "C"

SUB-PLATE
SCALE 4.0X

WIRE DUCT
SEE ENGRG. FOR CUT LIST
SCALE 2.0X



DETAIL "C"

WIRE DUCT
SEE ENGRG. FOR CUT LIST
SCALE 2.0X